

www.controlledairdesign.com - (800) 635 0298 - sales@controlledairdesign.com




HCF Horizontal Cartridge Filtration Collector

HCF-3000 Unit

The HCF Series Horizontal Cartridge Filtration Systems are designed to provide efficient, cost effective control of dry dusts, fumes, and general air borne particulate contaminants generated from sanding, grinding, welding, and other processes. Typically utilized for control of moderate to heavy concentrations of dry contaminates, the HCF series collectors are provided with self-cleaning, pulsejet filter cleaning to minimize maintenance and reduce replacement filter costs.

The ceiling mounted HCF series collectors are available in two configurations, un-ducted models for ambient air cleaning of the general plant air and ducted source capture systems for control of contaminates at the generating source.



<u>Unit Type</u>	Filter Area	<u>CFM</u>	LxWxH (in)	Weight (lbs)
HCF-3000 3HP Un-Ducted	960	3000	100x37x53	494
HCF-3030 3HP Ducted	960	3000	100x37*x44	494
HCF-3050 5HP Ducted	960	3000	100x37*x44	494
* not including arm box or collar				




Sanding and Grinding Applications
EDM Machining / Graphite
Ceramic Manufacturers
Woodshops

Welding, Fabricating and Machine Shops

*for our vertical, source-capture unit (VCF) visit our website





FEATURES

- Efficient, direct drive, backward curve plug fan blowers
- Option of a 3 HP or a 5 HP plug fan motor
- HEPA-like cartridge filters with 960 sq. ft. of filtration surface provide 99.9% efficiency
- Unique self-cleaning pulse jet system keeps filters clean, and helps reduce maintenance
- 2.75 sq. ft. of intake area on un-ducted systems
- Available as either a ducted unit or an un-ducted unit

OPTIONS

- Drum kit: To contain collected contaminates, includes: 55 gal drum, cover, locking ring, 8'x10" hose, and (2) 8" hose clamps
- Delay pulse timer kit: for lighter loads, allows you to program the pulsing in intervals of up to 6 hrs.
- Smart pulse kit: for use instead of the standard timer for on demand or continuous cleaning
- Plenum mount box: for ducted units, allows direct mounting of a mechanical arm to the collector (arm not included)
- Collar mount plates: for ducted units to run hard ducting to the collector